



## Boring bar set, steel, with IC, right-hand, Type: SET06



### Order data

Order number	260036 SET06
GTIN	4045197656629
Item class	29W

### Description

#### Supplied with:

Plastic case

### Technical description

ISO code toolholder	A0810J SCLCR/L06
ISO code toolholder	A1216M SCLCR/L06
ISO code toolholder	A0608H SCLCR/L06
ISO code toolholder	A1012K SCLCR/L06
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Head length L <sub>1</sub>	22 mm
Head length L <sub>1</sub>	27 mm
Head length L <sub>1</sub>	33 mm

Head length $L_1$	42 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Minimum pre-drill $\varnothing D_{\min}$	16 mm
Clamping height $L_2$	7 mm
Clamping height $L_2$	9 mm
Clamping height $L_2$	11 mm
Clamping height $L_2$	15 mm
Centre offset $L_3$	4 mm
Centre offset $L_3$	6 mm
Centre offset $L_3$	7 mm
Centre offset $L_3$	9 mm
Overall length $L$	100 mm
Overall length $L$	110 mm
Overall length $L$	125 mm
Overall length $L$	150 mm
Neck width $L_4$	6 mm
Neck width $L_4$	8 mm
Neck width $L_4$	10 mm
Neck width $L_4$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Boring bar steel Shank Ø / insert size 1216/06 mm	260032 1216/06
Boring bar steel Shank Ø / insert size 0608/06 mm	260032 0608/06
Boring bar steel Shank Ø / insert size 1012/06 mm	260032 1012/06
Boring bar steel Shank Ø / insert size 0810/06 mm	260032 0810/06
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500