



GlueMatic glue gun, Manufacturer's product number: 86954SET



Order data

Order number	083386 86954SET
GTIN	4007841086954
Item class	07E

Description

Version:

The GlueMatic hot glue gun is suitable for both large and small repair and craft projects. Simply glue, repair and save resources. Extremely precise professional gluing. With the GlueMatic 7011, you can fully exploit all the possibilities of hot gluing. In daily continuous use, a strong delivery quantity of 35 g/min., a short heating time of < 2 min. and temperature levels of 40 – 230°C are essential for processing of a wide range of materials.

Feature:

Power: 400 W

Temperature: 40 – 230°C

Warm-up time: 2 min

Feed rate: 35 gr/min

Temperature indicator: LCD-Display

Replaceable nozzle: Yes

Temperature accuracy: ± 5°C

Heating element: PTC heater

Voltage range (min): 220 V

Can be used for: Film, glass, rubber, wood, ceramic, leather, paper, cardboard, Plexiglas®, polystyrene, textiles

Melting temperature: 40 – 230°C

Cable length: 4 m

Dimensions (L x W x H): 230 x 70 x 290 mm

Variant: Case set

Net weight: 1.015 kg

Manufacturer's warranty: 1 year

EAN 4007841086954

Mains plug: Type F

Supplied with:

Includes 3 universal glue sticks, long nozzle and transport case.

Optional extras:

EAN 4007841 052928 GluePro fine long nozzle.

EAN 4007841 052935 GluePro long nozzle.

EAN 4007841 052737 GluePro long nozzle.

EAN 4007841 052430 glue sticks Ø 11 mm Fast.

EAN 4007841 052409 glue sticks Ø 11 mm Low Melt.

EAN 4007841 052416 glue sticks Ø 11 mm Acrylate.

No. 083388 size 052423 glue sticks Ø 11 mm Flex.

No. 083388 size 050092 glue sticks Ø 11 mm Universal.

Technical description

Power consumption	400 W
maximum delivery quantity	35 g/min
Warm-up time	2 min
#Plug version	Type F
Power supply	Mains-powered
Manufacturer's designation	PRO GlueMatic 7011
maximum Ø of the glue stick	11 mm
Type of product	Hot glue gun