

Garant
Lever lock toolholder, left-hand, Shank / insert size: 20/11 mm

Order data

Order number	250611 20/11
GTIN	4045197650542
Item class	21T

Technical description

Shim pins pack	259044 4
Insert size	11 mm
Shim punches pack	259047 3
Head length L ₁	28 mm
suitable indexable insert	DN.. 1104..
ISO code toolholder	PDJNR/L 2020K11
Shim	259031 7
Shank size	20 mm
Lever	259015 7
Functional width L ₄	25 mm
Lever screw	259018 6
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim punches set 10 pieces Type 3	259047 3
Lever Type 7	259015 7
Lever screw Type 6	259018 6
Set of shim pins 10 pieces Type 4	259044 4
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Shim Type 7	259031 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500