

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 8/06mm

Order data

Order number	260033 8/06
GTIN	4045197652300
Item class	21T

Technical description

Centre offset L_3	6 mm
Insert size	6 mm
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
ISO code toolholder	A08H SCLCR/L06
Minimum pre-drill $\varnothing D_{\min}$	10 mm
Overall length L	100 mm
Clamping height L_2	7 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500