

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 20/11 mm


Order data

Order number	250627 20/11
GTIN	4045197650627
Item class	21T

Technical description

Lever	259015 10
ISO code toolholder	A20Q PDUNR/L11
Centre offset L ₃	16 mm
Insert size	11 mm
Minimum pre-drill Ø D _{min}	25 mm
suitable indexable insert	DN.. 1104..
Lever screw	259018 12
Overall length L	180 mm
Clamping height L ₂	19 mm
Setting angle κ	93 degrees
Shank Ø D _s	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 10

259015 10

Lever screw Type 12

259018 12