

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 10/06mm


Order data

Order number	260033 10/06
GTIN	4045197652317
Item class	21T

Technical description

ISO code toolholder	A10K SCLCR/L06
suitable indexable insert	CC.. 0602..
Centre offset L_3	7 mm
Pack of insert screws	269028 22
Insert size	6 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500