



Pneumatic turbine grinder, Type: CP3T30



Order data

Order number	079313 CP3T30
GTIN	154518065218
Item class	03R

Description

Version:

Pneumatic turbine grinding machine for very heavy-duty applications, which keeps speed even at high loads. The turbine motor ensures a high power-to-weight ratio and does not require lubrication.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

recommended hose size (internal Ø)	13 mm
maximum air consumption	2010 l/min
maximum speed	12000 min ⁻¹
Connection thread	M14
Power supply	Pneumatic
Weight	2.2 kg
Output power	2300 W

Data sheet

maximum disc Ø	125 mm
Manufacturer's designation	CP3T30-120AA5V
Operating noise	78 dB(A)
Compressed air connection	3/8 in
maximum vibration to EN	2.6 m/s ²
Type of product	Angle grinder