

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 8/06 mm

Order data

Order number	260032 8/06
GTIN	4045197652225
Item class	21T

Description

Boring bar steel 8/06 mm Shank $\varnothing D_s$: 8 mm
 ISO code toolholder: A08H SCLCR/L06
 Setting angle κ : 95 °
 suitable indexable insert: CC.. 0602..
 Minimum pre-drill $\varnothing D_{min}$: 10 mm
 Centre offset L_3 : 6 mm

Technical description

ISO code toolholder	A08H SCLCR/L06
Pack of insert screws	269028 7
Insert size	6 mm
Centre offset L_3	6 mm
suitable indexable insert	CC.. 0602..
Minimum pre-drill $\varnothing D_{min}$	10 mm
Overall length L	100 mm
Clamping height L_2	7 mm
Setting angle κ	95 °
Shank $\varnothing D_s$	8 mm
Application type	right-hand
Boring depth up to	3xD

Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 5	269028 5
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws 10 pieces	269410
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500