

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 12/06 mm**

**Order data**

Order number	260033 12/06
GTIN	4045197652324
Item class	21T

**Description**

Boring bar steel 12/06 mm Shank  $\varnothing D_s$ : 12 mm  
 ISO code toolholder: A12L SCLCR/L06  
 Setting angle  $\kappa$ : 95 °  
 suitable indexable insert: CC.. 0602..  
 Minimum pre-drill  $\varnothing D_{\min}$ : 16 mm  
 Centre offset  $L_3$ : 9 mm

**Technical description**

Centre offset $L_3$	9 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A12L SCLCR/L06
Pack of insert screws	269028 22
Insert size	6 mm
Minimum pre-drill $\varnothing D_{\min}$	16 mm
Overall length L	140 mm
Clamping height $L_2$	11 mm
Setting angle $\kappa$	95 °
Shank $\varnothing D_s$	12 mm
Application type	left-hand
Boring depth up to	3xD

Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8