

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/09mm

Order data

Order number	260033 16/09
GTIN	4045197652331
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	20 mm
Insert size	9 mm
ISO code toolholder	A16Q SCLCR/L09
Pack of insert screws	269028 8
suitable indexable insert	CC.. 09T3..
Centre offset L_3	11 mm
Overall length L	180 mm
Clamping height L_2	14 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500