

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 20/09mm


Order data

| | |
|--------------|---------------|
| Order number | 260032 20/09 |
| GTIN | 4045197652263 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| ISO code toolholder | A20R SCLCR/L09 |
| Insert size | 9 mm |
| suitable indexable insert | CC.. 09T3.. |
| Pack of insert screws | 269028 8 |
| Minimum pre-drill $\varnothing D_{\min}$ | 25 mm |
| Centre offset L_3 | 13 mm |
| Overall length L | 200 mm |
| Clamping height L_2 | 18 mm |
| Setting angle κ | 95 degrees |
| Shank $\varnothing D_s$ | 20 mm |
| Standard | DIN 8024 |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |