

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	250626 20/11
GTIN	4045197650580
Item class	21T

Technical description

Centre offset L_3	16 mm
suitable indexable insert	DN.. 1104..
Insert size	11 mm
Lever	259015 10
Minimum pre-drill $\varnothing D_{\min}$	25 mm
ISO code toolholder	A20Q PDUNR/L11
Lever screw	259018 12
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 10

259015 10

Lever screw Type 12

259018 12