

**Garant**
**Toolholder straight – external 0°, left-hand, Shank width b: 20mm**

**Order data**

Order number	273801 20
GTIN	4045197499943
Item class	21W

**Description**
**Version:**

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

**Suitable for :**

Blade carriers No. 273813; 273816; 273818; 273821; 273823; 273825; 273827; 273829.

**Supplied with:**

Including assembly screws.

**Note:**

Tool holders must be ordered separately.

Head length L<sub>1</sub>: 38 mm

Overall length L: 138 mm

L<sub>2</sub>: 22.5 mm

Screw: 279815 9 (TX25; 6 Nm)

**Technical description**

L <sub>2</sub>	22.5 mm
Head length L <sub>1</sub>	38 mm
Screw	279815 9 (TX25; 6 Nm)
Shank width b	20 mm

Overall length L	138 mm
Application type	left-hand
Type of product	Clamping toolholder

---

## Accessories

Clamping screw Type 9	279815 9
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping screw	279910