

SICOMET
omniFIT**Flat gasket sealant, 50 ml, Manufacturer ID: FD10****Order data**

Order number	083337 FD10
GTIN	
Item class	08G

Description**Version:**

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

The liquid sealing material fills all gaps and ensures 100% surface contact. The connection is permanently sealed.

Application:

For sealing faces and flanged joints, compensates unevenness.

Note:

Before applying sealant, clean the surfaces with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Manufacturer's designation	FD10
Labelling of hazardous substances	GHS05: Corrosive

Labelling of hazardous substances	GHS08 harmful to health
Functional strength to	6 h
Dynamic viscosity	10000 - 15000 mPa·s
Working life after date of manufacture	24 mo
Storage temperature	8 - 28 °C
Suitable for application area	Liquid gasketing
Suitable for application area	Flange connection
Chemical basis	Dimethacrylate
minimum break-away torque	22 N·m
Capacity	50 ml
Suitable for material	Metal
Operating temperature range	-60 - 150 °C
Flashpoint	100 °C
Colour	green
Maximum gap size	0.3 mm
Strength class	medium strength
Density	1.05 g/cm ³
Product name attribute	50 ml
Type of product	Sealant