

## Garant

### Boring bar, left-hand, Ø DS: 25mm



#### Order data

Order number	273811 25
GTIN	4045197500045
Item class	21W

#### Description

##### Version:

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

##### Suitable for :

Blade carriers No. 273813; 273816; 273818; 273827.

##### Supplied with:

Including assembly screws.

##### Note:

Tool holders must be ordered separately.

Shank Ø D<sub>s</sub>: 25 mm

Centre offset L<sub>3</sub>: 15 mm

Head length L<sub>1</sub>: 38 mm

Overall length L: 213 mm

Screw: 279815 9 (TX25; 6 Nm)

#### Technical description

Centre offset L <sub>3</sub>	15 mm
Head length L <sub>1</sub>	38 mm
Screw	279815 9 (TX25; 6 Nm)
Overall length L	213 mm

Shank Ø D <sub>s</sub>	25 mm
Application type	left-hand
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping screw	279910
Clamping screw Type 9	279815 9