

Garant
Toolholder cranked – external 90°, right-hand, Shank width b: 16mm


Order data

Order number	273805 16
GTIN	4045197499967
Item class	21W

Description

Version:

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

Suitable for :

Blade carriers No. 273821; 273823; 273825; 273829.

Supplied with:

Including assembly screws.

Note:

Tool holders must be ordered separately.

Head length L_1 : 20.5 mm

Overall length L : 110 mm

L_2 : 29 mm

Screw: 279815 9 (TX25; 6 Nm)

Technical description

L_2	29 mm
Head length L_1	20.5 mm
Screw	279815 9 (TX25; 6 Nm)
Shank width b	16 mm

Overall length L	110 mm
Application type	right-hand
Type of product	Clamping toolholder

Accessories

Clamping screw	279910
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25	674248 TX25
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping screw Type 9	279815 9