


**Garant**

**Blade carrier, convex for face grooving, right-hand, Ø range Groove D1 / D2:  
43/60mm**

**Order data**

Order number	273815 43/60
GTIN	4045197500083
Item class	21W

**Description****Version:**

Extremely rigid connection and precise clamping due to serrated contact face between the toolholder and clamp.

**Application:**

In conjunction with toolholders No. 273800 to 273811.

**Spare part:**

Clamp screw No. 279815 9.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum Ø for the first groove /  $D_2$  = maximum Ø for the first cut.

Technology values should be reduced by 30 – 50% depending on the clamping situation and material.

Groove width w: 3 mm

maximum cutting depth  $t_{max}$ : 13 mm

**Technical description**

minimum 1st groove $\varnothing D_1$	43 mm
maximum cutting depth $t_{\max}$	13 mm
maximum 1st groove $\varnothing D_2$	60 mm
Application type	right-hand
Groove width w	3 mm
Type of product	Cartridges

---

## Accessories

Clamping screw	279910
Clamping screw Type 9	279815 9