

Garant

Toolholder cranked – external 90°, left-hand, Shank width b: 16mm



Order data

| | |
|--------------|---------------|
| Order number | 273806 16 |
| GTIN | 4045197499998 |
| Item class | 21W |

Description

Version:

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

Suitable for :

Blade carriers No. 273820; 273822; 273824; 273828.

Supplied with:

Including assembly screws.

Note:

Tool holders must be ordered separately.

Head length L_1 : 20.5 mm

Overall length L: 110 mm

L_2 : 29 mm

Screw: 279815 9 (TX25; 6 Nm)

Technical description

| | |
|-------------------|-----------------------|
| Shank width b | 16 mm |
| L_2 | 29 mm |
| Head length L_1 | 20.5 mm |
| Screw | 279815 9 (TX25; 6 Nm) |

| | |
|------------------|---------------------|
| Overall length L | 110 mm |
| Application type | left-hand |
| Type of product | Clamping toolholder |

Accessories

| | |
|---|-------------|
| Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm | 659906 1600 |
| Clamping screw | 279910 |
| Clamping screw Type 9 | 279815 9 |
| 8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm | 659874 50 |
| PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25 | 674248 TX25 |