


**Garant**

**Blade carrier, convex for face grooving, right-hand, Ø range Groove D1 / D2:  
51/67mm**

**Order data**

Order number	273812 51/67
GTIN	4045197576866
Item class	21W

**Description****Version:**

Extremely rigid connection and precise clamping due to serrated contact face between the toolholder and clamp.

**Application:**

In conjunction with toolholders No. 273800 to 273811.

**Spare part:**

Clamp screw No. 279815 9.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum Ø for the first groove /  $D_2$  = maximum Ø for the first cut.

Technology values should be reduced by 30 – 50% depending on the clamping situation and material.

Groove width w: 2 mm

maximum cutting depth  $t_{\max}$ : 13 mm

**Technical description**

maximum 1st groove $\varnothing D_2$	67 mm
maximum cutting depth $t_{\max}$	13 mm
minimum 1st groove $\varnothing D_1$	51 mm
Application type	right-hand
Groove width w	2 mm
Type of product	Cartridges

---

## Accessories

Clamping screw Type 9	279815 9
Clamping screw	279910