

Garant
Shrink-fit chuck, SK 40 A = 130, Clamping range \varnothing D1: 14mm

Order data

Order number	302266 14
GTIN	4045197646125
Item class	31A

Description
Version:

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

Application:

For clamping tools with parallel shank to h6 tolerance.
Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Technical description

Overhang dimension A	130 mm
Clamping \varnothing D ₁	14 mm
\varnothing D ₂	27 mm
External \varnothing D	34 mm
Adapter	SK 40 A = 130
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/12 mm	302416 32/12
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Shrink-fit unit Type SU1	354210 SU1
Pull studsealed, form B suitable for steep tapers 40	308650 40
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 32/14 mm	302412 32/14
Cooling unit Type CU1	354215 CU1
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M

Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/12 mm	302416 25/12
Basic tool mounting for SK for SK taper shank 40	354225 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Shrink-fit chuck extension 4.5° without length adjustment screw, with through coolant holes Ø d / Ø D1 32/14 mm	302414 32/14
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/14 mm	302416 25/14
Cooling adapter long 4.5° for clamping Ø 12,1-16 mm	354236 12,1-16
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 25/12 mm	302412 25/12
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/12 mm	302415 20/12
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/12 mm	302410 25/12
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/14 mm	302416 32/14
Cooling adapter short 4.5° for clamping Ø 12,1-16 mm	354235 12,1-16
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 25/14 mm	302412 25/14
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/14 mm	302410 25/14
	308625 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Shrink-fit chuck extension 4.5°with length adjustment
screw $\varnothing d / \varnothing D1$ 32/12 mm

302412 32/12

Pull studsealed suitable for steep tapers 40

308635 40

Pull studsealed, form B suitable for steep tapers 40

308620 40

Shrink-fit chuck extension 4.5°without length adjustment
screw $\varnothing d / \varnothing D1$ 32/14 mm

302410 32/14

Pull studForm B suitable for steep tapers 40

308640 40

Screening plate for coilSU1 for clamping \varnothing 12-20 mm

354240 12-20

Shrink-fit chuck extension 4.5°without length adjustment
screw $\varnothing d / \varnothing D1$ 32/12 mm

302410 32/12

Shrink fit chuck extension 3°, vibration-damped $\varnothing d / \varnothing D1$
25/14 mm

302417 25/14