

Garant
Shrink-fit chuck, SK 50 A = 120, Clamping range \varnothing D1: 10mm

Order data

Order number	302305 10
GTIN	4045197288608
Item class	31A

Description
Version:

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID/Balluffchip bore.**

Application:

For clamping tools with parallel shank to h6 tolerance.
Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Technical description

Overhang dimension A	120 mm
\varnothing D ₂	24 mm
Clamping \varnothing D ₁	10 mm
External \varnothing D	31.4 mm
Adapter	SK 50 A = 120
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Special pull stud with internal thread suitable for steep tapers 50	308740 50
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/10 mm	302410 25/10
Pull stud sealed suitable for steep tapers 50	308660 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 25/10 mm	302412 25/10
Basic tool mounting for SK for SK taper shank 50	354225 50
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 32/10 mm	302412 32/10
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50
Pull stud Form B suitable for steep tapers 50	308640 50
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/10 mm	302416 25/10
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/10 mm	302416 32/10
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50

Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/10 mm	302415 20/10
Shrink-fit chuck extension 4.5° without length adjustment screw, with through coolant holes Ø d / Ø D1 32/10 mm	302414 32/10
Cooling unit Type CU1	354215 CU1
Screening plate for coil SU1 for clamping Ø 6-12 mm	354240 6-12
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud sealed, form B suitable for steep tapers 50	308650 50
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/10 mm	302410 32/10
Cooling adapter short 4.5° for clamping Ø 9,1-12 mm	354235 9,1-12
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud sealed, form A suitable for steep tapers 50	308610 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud Form A suitable for steep tapers 50	308600 50
Shrink-fit unit Type SU1	354210 SU1
Cooling adapter long 4.5° for clamping Ø 9,1-12 mm	354236 9,1-12
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50