

## Garant

### Toolholder straight – external 0°, right-hand, Shank width b: 25mm



## Order data

Order number	273800 25
GTIN	4045197499929
Item class	21W

## Description

### Version:

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

### Suitable for :

Blade carriers No. 273812; 273815; 273817; 273820; 273822; 273824; 273826; 273828.

### Supplied with:

Including assembly screws.

### Note:

Tool holders must be ordered separately.

Head length L<sub>1</sub>: 38 mm

Overall length L: 163 mm

L<sub>2</sub>: 27.5 mm

Screw: 279815 9 (TX25; 6 Nm)

## Technical description

Shank width b	25 mm
Screw	279815 9 (TX25; 6 Nm)
Head length L <sub>1</sub>	38 mm
L <sub>2</sub>	27.5 mm

Overall length L	163 mm
Application type	right-hand
Type of product	Clamping toolholder

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping screw	279910
Clamping screw Type 9	279815 9
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25	674248 TX25