

**Pneumatic screwdriver, Type: S2465-L****Order data**

Order number	079162 S2465-L
GTIN	
Item class	03R

Description**Version:**

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. The S24 PRO pistol screwdrivers have a switch-off function to ensure high-quality screwdriving. These tools meet industry requirements for performance, accuracy and stability. The ergonomically well-balanced PRO small screwdrivers are handy, productive and offer simple torque adjustment.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

recommended hose size (internal Ø)	10 mm
Bit socket	F 6.3
Torque range	0.8-6.5 Nm
Compressed air connection	1/4 in
Length	232 mm
maximum screw Ø (8.8 - 12.9)	M5
maximum air consumption	870 l/min

Data sheet

maximum speed	1000 min ⁻¹
Operating noise	87 dB(A)
Power supply	Pneumatic
Weight	0.8 kg
Format	Rod
maximum vibration to EN	<2.5 m/s ²
Connection thread	NPT
Type of product	Screwdriver