

**LED cordless lamp 0 version without battery, 18 V, Type: M18TLED****Order data**

Order number	073211 M18TLED
GTIN	4002395380220
Item class	07A

Description**Version:**

Robust Li-Ion battery lights with high light intensity. With adjustable LED head
Lamp head adjustable 135°.

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Manufacturer's designation	M18TLED-0
Battery voltage	18 V
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	300 g
Illumination	120 lm

Bulb	LED module
Power supply	Rechargeable battery-powered
Pivot range	135 degrees
ATEX zone	no
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp

Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C