


WCHX 170608, Type: ALU

Order data

| | |
|--------------|---------------|
| Order number | 268498 ALU |
| GTIN | 4045197471062 |
| Item class | 21K |

Description
Suitable for :

Boring tool No. 268463 – 268468, size 33.

suitable for tool \varnothing D: 33 mm

Grade: HU70AL

Cutting speed v_c main application: 300 - 600 m/min

Cutting speed v_c secondary application: 180 m/min

Technical description

| | |
|---|--------------------------------|
| Cutting speed v_c main application | 300 - 600 m/min |
| Cutting speed v_c secondary application | 180 m/min |
| Secondary application | K |
| Main application | N |
| Type | ALU |
| Grade | HU70AL |
| Tool material | Carbide |
| Series | 5 in 1 turning and boring tool |

| | |
|-----------------------------------|---------------|
| ISO code indexable insert | TOHX 090202 L |
| suitable for tool \varnothing D | 33 mm |