


WCHX 170608, Type: SM

Order data

Order number	268498 SM
GTIN	4045197471086
Item class	21K

Description
Suitable for :

Boring tool No. 268463 – 268468, size 33.

suitable for tool \varnothing D: 33 mm

Grade: HB7120

Cutting speed v_c main application: 110 - 220 m/min

Cutting speed v_c secondary application: 110 - 140 m/min

Technical description

Type	SM
Cutting speed v_c main application	110 - 220 m/min
Cutting speed v_c secondary application	110 - 140 m/min
Secondary application	M
Main application	P
Grade	HB7120
Tool material	Carbide
Series	5 in 1 turning and boring tool

ISO code indexable insert	TOHX 090202 L
suitable for tool \varnothing D	33 mm