

**Garant**
**Boring bar HSS, left-hand, Overhang / insert size: 46/S4mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 268706 46/S4  |
| GTIN         | 4045197591951 |
| Item class   | 21V           |

**Technical description**

|  |                               |
|--|-------------------------------|
| Centre offset $L_3$                      | 3 mm                          |
| Pack of insert screws                    | 269028 10                     |
| Minimum pre-drill $\varnothing D_{\min}$ | 5.78 mm                       |
| suitable indexable insert                | CDCT S4010.                   |
| ISO code toolholder                      | AH05X SCLDR/LS4               |
| Insert size                              | 4 mm                          |
| Overall length L                         | 65 mm                         |
| Clamping height $L_2$                    | 4.6 mm                        |
| Setting angle $\kappa$                   | 95 degrees                    |
| Shank $\varnothing D_s$                  | 5 mm                          |
| Standard                                 | Works standard                |
| Application type                         | left-hand                     |
| Boring depth up to                       | 5×D                           |
| Tool material                            | HSS                           |
| Through-coolant                          | yes                           |
| Application                              | Internal longitudinal turning |
| Type of product                          | Boring bar                    |

---

**Accessories**

|  |            |
|--|------------|
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6                             | 674248 TX6 |
| Set of insert screws Type 10   | 269028 10  |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm | 659957 200 |