



LED cordless lamp 0 version without battery, 18 V, Type: M18AL



Order data

Order number	073211 M18AL
GTIN	4002395380534
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity.

- **Handy and very robust cordless lamp with high illumination intensity of 1500 Lumen.**
- **2 brightness levels.**
- **Integral handle. Can be hung vertically and horizontally on a 13 mm Ø pipe.**

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Manufacturer's designation	M18AL-0
Illumination step 2	780 lm
Battery voltage	18 V
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	1700 g

Power supply	Rechargeable battery-powered
Illumination	1500 lm
Bulb	LED module
Overall length	220 mm
ATEX zone	no
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp

Accessories

Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18