

**Garant**
**Boring bar HSS, left-hand, Overhang / insert size: 50/S4mm**

**Order data**

Order number	268706 50/S4
GTIN	4045197591968
Item class	21V

**Technical description**

ISO code toolholder	AH06X SCLDR/LS4
Insert size	4 mm
Centre offset $L_3$	3.5 mm
Minimum pre-drill $\varnothing D_{\min}$	6.92 mm
Pack of insert screws	269028 10
suitable indexable insert	CDCT S4010.
Overall length L	75 mm
Clamping height $L_2$	5.54 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 10	269028 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200