

Garant
Boring bar HSS, left-hand, Overhang / insert size: 66/S4mm

Order data

Order number	268706 66/S4
GTIN	4045197591975
Item class	21V

Technical description

Pack of insert screws	269028 10
Insert size	4 mm
suitable indexable insert	CDCT S4010.
Minimum pre-drill $\varnothing D_{\min}$	9.05 mm
ISO code toolholder	AH08H SCLDR/LS4
Centre offset L_3	4.5 mm
Overall length L	100 mm
Clamping height L_2	7.49 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 10	269028 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200