

Garant**WCHX 10T308, Type: UNI**

Order data

| | |
|--------------|---------------|
| Order number | 268494 UNI |
| GTIN | 4045197470980 |
| Item class | 21K |

Description

Suitable for:

Boring tool No. 268463 – 268468, size 20.

Technical description

| | |
|--------------------------------------|------------------------------|
| Type | UNI |
| Main application | UNI |
| Corner radius | 0.2 mm |
| Cutting speed v_c main application | 65 - 200 m/min |
| Grade | HB7130 |
| Tool material | Carbide |
| ISO code indexable insert | WCHX 10T308 |
| Number of changes/inserts | 3 |
| suitable for tool dia. D_c | 20 mm |
| Type of product | Indexable insert for turning |

