

Garant
Boring bar HSS, right-hand, Overhang / insert size: 46/S4mm

Order data

Order number	268702 46/S4
GTIN	4045197591913
Item class	21V

Technical description

Centre offset L_3	3 mm
Pack of insert screws	269028 10
Minimum pre-drill $\varnothing D_{\min}$	5.78 mm
ISO code toolholder	AH05X SCLDR/LS4
Insert size	4 mm
suitable indexable insert	CDCT S4010.
Overall length L	65 mm
Clamping height L_2	4.6 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 10	269028 10
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200