



Hydraulic chuck extension, L = 150 mm, Shank \varnothing d / Clamping range \varnothing D1: 20/20mm



Order data

Order number	302375 20/20
GTIN	2050001740953
Item class	33W

Description

Version:

With axial length adjustment. Flexible due to use of reducing sleeves.

Application:

Suitable for hydraulic chucks and collet chucks.

Optional extras:

Reducing sleeves No. 302135 – 302187.

Technical description

Adjustment travel V	10 mm
Overhang dimension A	100 mm
Shank \varnothing d	20 mm
Clamping \varnothing D ₁	20 mm
L ₁	51 mm
Thread M	M16×1
External \varnothing D	31.5 mm
Overall length L	150 mm
Product name attribute	L = 150 mm
Type of product	Hydraulic clamping chuck accessories

Accessories

Slotted reducing adaptersealed Clamping range Ø D1 8 mm	302160 8
Slotted reducing adaptersealed Clamping range Ø D1 10 mm	302160 10
Slotted reducing adaptersealed Clamping range Ø D1 6 mm	302160 6
Slotted reducing adaptersealed Clamping range Ø D1 14 mm	302160 14
Slotted reducing adapterwith cooling Clamping range Ø D1 4 mm	302155 4
Slotted reducing adapterwith cooling Clamping range Ø D1 12 mm	302155 12
Slotted reducing adapterwith cooling Clamping range Ø D1 6 mm	302155 6
Slotted reducing adaptersealed Clamping range Ø D1 16 mm	302160 16
Slotted reducing adapterwith cooling Clamping range Ø D1 3 mm	302155 3
Slotted reducing adapterwith cooling Clamping range Ø D1 16 mm	302155 16
Slotted reducing adapterwith cooling Clamping range Ø D1 5 mm	302155 5
Slotted reducing adapterwith cooling Clamping range Ø D1 14 mm	302155 14
Slotted reducing adaptersealed Clamping range Ø D1 5 mm	302160 5
Slotted reducing adaptersealed Clamping range Ø D1 4 mm	302160 4
Slotted reducing adaptersealed Clamping range Ø D1 3 mm	302160 3
Slotted reducing adaptersealed Clamping range Ø D1 12 mm	302160 12

Slotted reducing adapterwith cooling Clamping range Ø
D1 10 mm

302155 10

Slotted reducing adapterwith cooling Clamping range Ø
D1 8 mm

302155 8