



Hydraulic chuck extension, L = 150 mm, Shank \varnothing d / Clamping range \varnothing D1: 32/20mm



Order data

Order number	302375 32/20
GTIN	2050001740960
Item class	33W

Description

Version:

With axial length adjustment. Flexible due to use of reducing sleeves.

Application:

Suitable for hydraulic chucks and collet chucks.

Optional extras:

Reducing sleeves No. 302135 – 302187.

Technical description

Thread M	M16×1
Overhang dimension A	90 mm
Shank \varnothing d	32 mm
Adjustment travel V	10 mm
L ₁	51 mm
Clamping \varnothing D ₁	20 mm
External \varnothing D	31.5 mm
Overall length L	150 mm
Product name attribute	L = 150 mm
Type of product	Hydraulic clamping chuck accessories

Accessories

Slotted reducing adapterwith cooling Clamping range Ø D1 16 mm	302175 16
Slotted reducing adapterwith cooling Clamping range Ø D1 18 mm	302175 18
Slotted reducing adapterwith cooling Clamping range Ø D1 25 mm	302175 25
Slotted reducing adaptersealed Clamping range Ø D1 16 mm	302180 16
Slotted reducing adaptersealed Clamping range Ø D1 10 mm	302180 10
Slotted reducing adapterwith cooling Clamping range Ø D1 14 mm	302175 14
Slotted reducing adaptersealed Clamping range Ø D1 18 mm	302180 18
Slotted reducing adaptersealed Clamping range Ø D1 8 mm	302180 8
Slotted reducing adapterwith cooling Clamping range Ø D1 12 mm	302175 12
Slotted reducing adaptersealed Clamping range Ø D1 6 mm	302180 6
Slotted reducing adaptersealed Clamping range Ø D1 20 mm	302180 20
Slotted reducing adapterwith cooling Clamping range Ø D1 6 mm	302175 6
Slotted reducing adaptersealed Clamping range Ø D1 12 mm	302180 12
Slotted reducing adapterwith cooling Clamping range Ø D1 10 mm	302175 10
Slotted reducing adapterwith cooling Clamping range Ø D1 20 mm	302175 20
Slotted reducing adaptersealed Clamping range Ø D1 14 mm	302180 14

Slotted reducing adaptersealed Clamping range \varnothing D1 25 mm

302180 25

Slotted reducing adapterwith cooling Clamping range \varnothing D1 8 mm

302175 8