

Garant
Boring bar HSS, right-hand, Overhang / insert size: 66/07mm

Order data

Order number	268812 66/07
GTIN	4045197591999
Item class	21V

Technical description

suitable indexable insert	TDAT 07010.
Centre offset L_3	4.8 mm
ISO code toolholder	AH08H STLDR/L07
Pack of insert screws	269028 12
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	9.14 mm
Overall length L	100 mm
Clamping height L_2	7.49 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 12	269028 12
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500