

**LOCTITE****Thread sealant stick, 19 g, Manufacturer ID: 561**

## Order data

Order number	083311 561
GTIN	5010266383019
Item class	04L

## Description

### Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

The **stick** with pasty sealant is economical in consumption, no drips after use.

### Application:

Improved bonding of suckers.

### Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

## Technical description

minimum break-away torque	2 Nm
Manufacturer's designation	LOCTITE 561
for imperial thread size	3 in

Labelling of hazardous substances	GHS07: Exclamation mark
for thread size M to	M80
Functional strength to	24 h
Suitable for material	Metal
Suitable for application area	Maintenance
Touch dry after	60 min
Colour	white
Shape	semi-solid
Storage temperature	8 - 28 °C
Chemical basis	Methacrylate ester
Operating temperature range	-55 - 150 °C
Capacity	19 ml
Working life after date of manufacture	48 mo
Strength class	low strength
Density	1.14 g/cm <sup>3</sup>
Product name attribute	19 g
Type of product	Sealant