



Multi-function product, Type: 25000



Order data

Order number	083005 25000
GTIN	5032227490253
Item class	08E

Description

Version:

WD-40® multi-purpose oil helps maintain the value of machines and tools during maintenance work. The product displaces moisture, protects metal from rust and corrosion, penetrates into trapped parts and releases jammed mechanisms and moving parts. It removes grease, soot and other dirt from surfaces and prevents squeaking. Contains no silicone, resin or PTFE, temperature application range -50 to +150°C, non-conductive, 360° valve for use from any position.

Application:

- **Rust remover with penetrating capillary action – quickly releases seized bolts and nuts.**
- **Cleaner – loosens stubborn dirt, without sticking or gumming up.**
- **Lubricant for all sliding surfaces, precision mechanics, hinges, Bowden cables, locks and catches.**
- **Corrosion protection – WD-40 penetrates under moisture and into the pores of the material to be protected, thus preserving it. Delicate and expensive tools retain their value.**
- **Contact spray – displaces moisture from electrical components.**

By wide-scale use **of the spray dispenser No. 083006 or No. 083509 – 083517** for economic application over large surfaces.

Note:

Approved by: **Rolls Royce, Daimler, Airbus, VW** amongst others.

Not available in all countries. Express delivery not possible.

Technical description

Shape	liquid
Labelling of hazardous substances	GHS08 harmful to health
Labelling of hazardous substances	GHS07 caution
Labelling of hazardous substances	GHS02: Flame
Version	Can
Contents	25 l
Version	Can
Type of product	Multi-function oil / universal oil