

**Garant**
**Boring bar HSS, left-hand, Overhang / insert size: 66/S5mm**

**Order data**

Order number	268726 66/S5
GTIN	4045197545824
Item class	21V

**Technical description**

Centre offset $L_3$	6.4 mm
Pack of insert screws	269028 6
Head length $L_1$	32 mm
Neck width $L_4$	8 mm
suitable indexable insert	GPCT S5010.
Minimum pre-drill $\varnothing D_{\min}$	10.72 mm
Insert size	5 mm
ISO code toolholder	AH0812H SGLPR/LS5
Overall length L	100 mm
Clamping height $L_2$	11.15 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 6	269028 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500