



**Internal corner turning tool right-hand similar to DIN 4954, HSS E, Shank Ø: 6mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 296400 6      |
| GTIN         | 4069515024617 |
| Item class   | 22E           |

## Description

### Version:

All dimensions **welded**.

### Application:

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

## Technical description

|                  |              |
|------------------|--------------|
| for bores from Ø | 16 mm        |
| Overall length   | 125 mm       |
| Shank Ø          | 6 mm         |
| Tool material    | HSS E        |
| Type of product  | Turning tool |