



Internal corner turning tool right-hand similar to DIN 4954, HSS E, Shank Ø: 8mm



Order data

Order number	296400 8
GTIN	4069515024662
Item class	22E

Description

Version:

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

Overall length	140 mm
Shank Ø	8 mm
for bores from Ø	18 mm
Tool material	HSS E
Type of product	Turning tool