

Garant**GARANT Master Mute boring bar shank HSK-T vibration damping, HSK-T 63,
Shank Ø / usable length L1: 40/210mm****Order data**

Order number	265060 40/210
GTIN	4069515026383
Item class	29E

Description**Version:**

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Suitable for:

GARANT Master Mute exchangeable cutting heads No. 265100 – 265377.

Note:

The usable length is extended by the length L of the respective exchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Overhang dimension A	266 mm
Shank Ø	40 mm
Assembly bolt set	269026 3
Series	Master Mute
Number of coolant channels	3
Adapter	HSK-T 63
Vibration	damped
Arbor standard	ISO 26623-1
Arbor standard	ISO 12164-3

Data sheet

Through-coolant	yes
Type of product	Boring bar shanks