



**GARANT Master Mute boring bar shank PSC vibration damping, PSC 40,
Shank Ø / usable length L1: 20/90mm**



Order data

Order number	265062 20/90
GTIN	4069515026529
Item class	29E

Description

Version:

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Suitable for:

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

Note:

The usable length is extended by the length L of the respective interchangeable cutting head.
Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Assembly bolt set	269026 1
Shank Ø	20 mm
Overhang dimension A	126 mm
Reach L ₁	90 mm
Series	Master Mute
Number of coolant channels	3
Adapter	PSC 40
Vibration	damped
Arbor standard	ISO 26623-1

Data sheet

Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar shanks