



**GARANT Master Mute boring bar shank PSC vibration damping, PSC 40,  
Shank Ø / usable length L1: 25/230mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 265062 25/230 |
| GTIN         | 4069515026567 |
| Item class   | 29E           |

## Description

**Version:**

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

**Suitable for:**

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

**Note:**

The usable length is extended by the length L of the respective interchangeable cutting head.  
Use **only with internal cooling** (temperature resistance of up to max. 100°C).

## Technical description

|                            |             |
|----------------------------|-------------|
| Overhang dimension A       | 266 mm      |
| Shank Ø                    | 25 mm       |
| Assembly bolt set          | 269026 4    |
| Reach L <sub>1</sub>       | 230 mm      |
| Series                     | Master Mute |
| Number of coolant channels | 3           |
| Adapter                    | PSC 40      |
| Vibration                  | damped      |
| Arbor standard             | ISO 26623-1 |

## Data sheet

|                 |                   |
|-----------------|-------------------|
| Arbor standard  | ISO 12164-3       |
| Through-coolant | yes               |
| Type of product | Boring bar shanks |