

**Garant****GARANT Master Mute boring bar shank PSC vibration damping, PSC 80,  
Shank Ø / usable length L1: 40/210mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 265065 40/210 |
| GTIN         | 4069515027076 |
| Item class   | 29E           |

**Description****Version:**

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

Shank version Ø 50 mm and Ø 60 mm in right-hand version. Left-hand version available on request.

**Suitable for:**

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

**Note:**

The usable length is extended by the length L of the respective interchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

**Technical description**

|                            |             |
|----------------------------|-------------|
| Overhang dimension A       | 240 mm      |
| Shank Ø                    | 40 mm       |
| Assembly bolt set          | 269026 3    |
| Reach L <sub>1</sub>       | 210 mm      |
| Series                     | Master Mute |
| Number of coolant channels | 3           |
| Adapter                    | PSC 80      |
| Vibration                  | damped      |

## Data sheet

|                 |                   |
|-----------------|-------------------|
| Arbor standard  | ISO 12164-3       |
| Arbor standard  | ISO 26623-1       |
| Through-coolant | yes               |
| Type of product | Boring bar shanks |