



**GARANT Master Mute boring bar shank PSC vibration damping, PSC 80,
Shank Ø / usable length L1: 60/570mm**



Order data

Order number	265065 60/570
GTIN	4069515027151
Item class	29E

Description

Version:

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Shank version Ø 50 mm and Ø 60 mm in right-hand version. Left-hand version available on request.

Suitable for:

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

Note:

The usable length is extended by the length L of the respective interchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Assembly bolt set	269026 3
Shank Ø	60 mm
Overhang dimension A	602 mm
Reach L ₁	570 mm
Series	Master Mute
Number of coolant channels	1
Adapter	PSC 80
Vibration	damped

Data sheet

Arbor standard	ISO 12164-3
Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar shanks