



Rope light, Type: ROPE-LIGHT



Order data

Order number	081605 ROPE-LIGHT
GTIN	5708997358160
Item class	08C

Description

Version:

The "ROPE LIGHT" is a 25 m long, flicker-free and approved rope light with an output of 20,000 lumens. The light can be used both for orientation and as a work light. The drum enables the light to be conveniently rolled up. ROPE LIGHT is operated at low voltage (48 V DC), so there is no risk of an electric shock if the rope is accidentally trapped or cut.

Note:

To prevent overheating, always fully uncoil the rope light from the drum before you connect it to the power supply.

Technical description

Overall length	25000 mm
Power supply	Mains-powered
Bulb	LED module
Nominal voltage	48 V
IP Index of Protection	IP 65
Illumination	20000 lm
Type of product	Area light

