



Self-levelling cross-hair laser GCL, Type: GCL12V



Order data

Order number	468488 GCL12V
GTIN	4053423303360
Item class	46T

Description

Version:

Compact cross-hair laser with self-levelling laser lines. Quick horizontal and vertical alignment of lines. Robust design soft-grip coating protects against impact loads. Dust-proof and splash-proof. In addition, two vertical plumb-line points. **Green cross-hairs** for optimum visibility even under poor lighting conditions. Bluetooth® interface for precise working by remote control without touching the device. Can be operated with rechargeable battery (supplied) or batteries. Large working range up to 50 m using the LR 7 Professional receiver (accessories).

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

12 V Li-ion battery, charger, multi-function holder, laser target plate, protective bag and transport case.

Technical description

Error limit	±0.3 mm/m
Type of rechargeable battery	Lithium-ion

Data sheet

Interface	Bluetooth® interface
Range	25 m
Battery capacity	2 Ah
Battery voltage	12 V
Threaded socket for stand	1/4 in
IP Index of Protection	IP 65
Range with receiver	50 m
Manufacturer's designation	GCL12V
Power supply	Battery-powered
Length	152 mm
Laser class	2
Series	GCL
Packaging	Carrying case
Number of rechargeable batteries contained	1
Width	68 mm
#Article no of the battery / rechargeable battery fitted	073851 B12
Colour of the laser	green
Levelling range	±4 degrees
Height	116 mm
Weight	590 g
Type of product	Cross laser