

AEG**, impact wrench, cordless impact wrench**

Order data

Order number	070229 BSB18SBL22
GTIN	4058546403430
Item class	07A

Description

Version:

2-Speed cordless combi drill with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screwdriving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**

Sub-Compact drill/driver, for the ultimate in user productivity and ergonomics. Suitable for use in confined spaces.

Note:

See No. 073841 – No. 073848 for suitable batteries and chargers.

Technical description

Battery capacity	2 Ah
Weight	1.4 kg
maximum vibration to EN without hammer drill function	<2,5 m/s ²
Power supply	Mains operated

Data sheet

Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in concrete	13 mm
maximum speed 1st speed	0 - 450 min ⁻¹
maximum torque soft	32 Nm
Packaging	Carrying case
Manufacturer's designation	BSB 18SBL2-202C
typical application	Heavy Duty
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Motor design	Brushless
Number of rechargeable batteries contained	2
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 2nd speed	1750 min ⁻¹
maximum twist drill size Ø in wood	40 mm
maximum torque hard	65 Nm
maximum twist drill size Ø in steel	13 mm
Type of product	limpact drill /screwdriver