

**AEG****Cordless circular saw, Type: BKS18SBL****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 078221 BKS18SBL |
| GTIN         | 4058546374549   |
| Item class   | 07A             |

**Description****Version:**

Brushless Sub-Compact circular saw for fast, powerful sawing in a compact size.

**Supplied with:**

Without battery and charger.

**Technical description**

|                                                      |                              |
|------------------------------------------------------|------------------------------|
| maximum speed                                        | 5000 min <sup>-1</sup>       |
| Power supply                                         | Rechargeable battery-powered |
| Saw blade Ø                                          | 165 mm                       |
| Weight                                               | 2.9 kg                       |
| Saw blade bore Ø                                     | 20 mm                        |
| suitable battery - supplier / battery type / voltage | AEG type AS 18 V             |
| Version                                              | Hand-held circular saw       |
| maximum vibration to EN                              | <2.5 m/s <sup>2</sup>        |
| Type of rechargeable battery                         | Lithium-ion                  |

## Data sheet

|                                            |             |
|--------------------------------------------|-------------|
| Number of rechargeable batteries contained | 0           |
| maximum cutting depth 90°                  | 57 mm       |
| Manufacturer's designation                 | BKS 18SBL-0 |
| Battery voltage                            | 18 V        |
| Type of product                            | Saw         |