

AEG

Impact wrench 18 V, cordless impact wrench, max. screw Ø M16, toolholder external square drive 1/2 inch



Order data

Order number	074016 BSS18HTF12
GTIN	4058546483005
Item class	07A

Description

Version:

Powerful 18 V cordless impact wrench with 1/2 inch square toolholder.

- **LED illumination of the working area.**
- **Handle with soft-grip coating.**
- **Belt hook.**
- **Torque adjustment in 4 stages including auto-stop for optimum tightening and releasing of wheel nuts.**
- **Brushless motor.**

Supplied with:

Without battery and without charger, in a cardboard box.

Note:

See 073841 – 073848 for suitable rechargeable batteries and chargers

Technical description

typical application	Heavy Duty
Weight	3.05 kg

Data sheet

maximum torque	1220 Nm
Battery voltage	18 V
Tool arbor drive profile	External square drive
Number of rechargeable batteries contained	0
Manufacturer's designation	BSS 18HTF12BL-0
Type of rechargeable battery	Lithium-ion
Number of impacts	0 - 1900 min ⁻¹
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Tool arbor size	1/2 in
Type of product	Impact wrench